

Eaton BKLGE500T

Catalog Number: BKLGE500T

MAIN BKR KIT 480V MAX 1 OR 3PH 500A LG TOP MOUNTING



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Pow-R-Stock main breaker kit	BKLGE500T
UPC	Product Length/Depth
786687010814	5.5 in
Product Height	Product Width
12 in	5.5 in
Product Weight	Certifications
16 lb	UL Listed

defaultTaxonomyAttributeLabel

Type

Breaker Kit

Amperage Rating

500A

Bus material

Copper

Bus Rating

600 A

Circuit breaker type

LG

Feed type

Top

Mounting

Top

Nominal frequency

50 Hz

Number Of Poles

Three-pole

Operating Temperature

40°C

Phase

Single-phase, three-phase

Short-circuit rating

35 A

Voltage rating

277 V, 480 V

Wire size

#4 AWG-350 kcmil

Application

Commercial construction

Circuit breaker rating

500

Indicators

Local

Interrupt rating

Resources

Multimedia

[Pow-R-Line Xpert family overview](#)

Specifications and datasheets

[Eaton Specification Sheet - BKLGE500T](#)

35 kAIC

Number of conductors

1 per phase

Operator

Manual

Primary voltage

277Y/480 V

Series

C

Trip rating

500

Voltage - max

600



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia