

Bussmann series North American fuse links & fuse holders.

BAF



FNM



FNA



KTK-R



SC



Item no.	Amp rating	Size	Volts	Type	Box qty		
Supplementary power fuse links (ferrule)							
BBS (A)	1/10 to 5	10 x 35mm	600	Fast	10		
	6, 7, 8, 10		250				
	12, 15, 20, 25, 30		48				
KTQ (A)	1, 1.6, 2, 3, 4, 5, 6		250	T/Delay			
BAF (A)	2/10 to 15	10 x 38mm	250	Fast	10		
	20, 25, 30		125				
BAN (A)	1, 2, 4, 6, 8, 10, 12, 15, 20, 25, 30		250	Fast			
KTK (A)	1/10 to 50		600	Fast			
DCM (A)	1/10 to 30		600V ac / dc	Fast			
KLM (A)	1/10 to 30		690	Fast			
FNM (A)	0.1, 0.125, 0.15, 0.2, 0.25, 0.3, 0.4, 0.5, 0.6, 0.75, 1, 1.125, 1.25, 1.5, 2, 2.25, 2.5, 2.8, 3, 3.25, 3.5, 4, 4.5, 5, 5.8, 6, 6.25, 7, 8, 9, 10,		250	T/Delay			
	12, 15		125				
	20, 25, 30		32				
	FNQ (A)		1/10 to 30	500		T/Delay	
FNA (A)	1/10 to 8/10		250	T/Delay			
	1 to 15		125				
	20 to 30		32				
DMM-D-(A)	44/100 & 11			1000		Fast	

Item no.	Amp	Volts	Poles	Box qty
Fuseholders to suit supplementary power fuse links.				
BM6031SQ	30	600	1	1
BM6033SQ			3	

Item no.	Amp rating	Size	Volts	Type	Box qty
Supplementary power fuse links - rejection - Class CC.					
KTK-R (A)	1/10 to 30	10 X 38mm	600	Fast	10
LP-CC (A)	1/4 to 30			T/Delay	
FNQ-R (A)	1/4 to 30				

Item no.	Amp	Volts	Poles	Box qty
Fuseholders to suit supplementary power fuse links - Class CC.				
BC6031SQ	30	600	1	1
BC6033SQ			3	

Item no.	Amp rating	Size	Volts	Type	Box qty
Supplementary power fuse links - Class G.					
SC	1/2 to 20	10 X 33	480	T/Delay	
	25, 30	10 X 42			
	35 to 60	10 X 57			

Bussmann series North American fuse links & fuse holders.

BAF



FNM



FNA



KTK-R



SC



Item no.	Amp rating	Size	Volts	Type	Box qty
Supplementary power fuse links (ferrule)					
BBS (A)	1/10 to 5	10 x 35mm	600	Fast	10
	6, 7, 8, 10		250		
	12, 15, 20, 25, 30		48		
KTQ (A)	1, 1.6, 2, 3, 4, 5, 6		250	T/Delay	
BAF (A)	2/10 to 15		250	Fast	
	20, 25, 30		125		
BAN (A)	1, 2, 4, 6, 8, 10, 12, 15, 20, 25, 30		250	Fast	
KTK (A)	1/10 to 50		600	Fast	
DCM (A)	1/10 to 30		600V ac / dc	Fast	
KLM (A)	1/10 to 30		690	Fast	
FNM (A)	0.1, 0.125, 0.15, 0.2, 0.25, 0.3, 0.4, 0.5, 0.6, 0.75, 1, 1.125, 1.25, 1.5, 2, 2.25, 2.5, 2.8, 3, 3.25, 3.5, 4, 4.5, 5, 5.8, 6, 6.25, 7, 8, 9, 10,	10 x 38mm	250	T/Delay	10
	12, 15		125		
	20, 25, 30		32		
FNQ (A)	1/10 to 30		500	T/Delay	
FNA (A)	1/10 to 8/10		250	T/Delay	
	1 to 15		125		
	20 to 30		32		
DMM-D-(A)	44/100 & 11		1000	Fast	

Item no.	Amp	Volts	Poles	Box qty
Fuseholders to suit supplementary power fuse links.				
BM6031SQ	30	600	1	1
BM6033SQ			3	

Item no.	Amp rating	Size	Volts	Type	Box qty
Supplementary power fuse links - rejection - Class CC.					
KTK-R (A)	1/10 to 30	10 X 38mm	600	Fast	10
LP-CC (A)	1/4 to 30			T/Delay	
FNQ-R (A)	1/4 to 30				

Item no.	Amp	Volts	Poles	Box qty
Fuseholders to suit supplementary power fuse links - Class CC.				
BC6031SQ	30	600	1	1
BC6033SQ			3	

Item no.	Amp rating	Size	Volts	Type	Box qty
Supplementary power fuse links - Class G.					
SC	1/2 to 20	10 X 33	480	T/Delay	
	25, 30	10 X 42			
	35 to 60	10 X 57			