

Bussmann series North American fuse links & fuse holders.



BAF

Item no.	Amp rating	Size	Volts	Type	Box qty
<b>Supplementary power fuse links (ferrule)</b>					
<b>BBS (A)</b>	1/10 to 5	10 x 35mm	600	Fast	10
	6, 7, 8, 10		250		
	12, 15, 20, 25, 30		48		
<b>KTQ (A)</b>	1, 1.6, 2, 3, 4, 5, 6		250	T/Delay	
<b>BAF (A)</b>	2/10 to 15		250	Fast	
	20, 25, 30		125		
<b>BAN (A)</b>	1, 2, 4, 6, 8, 10, 12, 15, 20, 25, 30		250	Fast	
<b>KTK (A)</b>	1/10 to 50		600	Fast	
<b>DCM (A)</b>	1/10 to 30		600V ac / dc	Fast	
<b>KLM (A)</b>	1/10 to 30		690	Fast	
<b>FNM (A)</b>	0.1, 0.125, 0.15, 0.2, 0.25, 0.3, 0.4, 0.5, 0.6, 0.75, 1, 1.125, 1.25, 1.5, 2, 2.25, 2.5, 2.8, 3, 3.25, 3.5, 4, 4.5, 5, 5.8, 6, 6.25, 7, 8, 9, 10,	10 x 38mm	250	T/Delay	10
	12, 15		125		
	20, 25, 30		32		
<b>FNQ (A)</b>	1/10 to 30		500	T/Delay	
<b>FNA (A)</b>	1/10 to 8/10		250	T/Delay	
	1 to 15		125		
	20 to 30		32		
<b>DMM-D-(A)</b>	44/100 & 11		1000	Fast	



FNM



FNA

Item no.	Amp	Volts	Poles	Box qty
<b>Fuseholders to suit supplementary power fuse links.</b>				
<b>BM6031SQ</b>	30	600	1	1
<b>BM6033SQ</b>			3	

Item no.	Amp rating	Size	Volts	Type	Box qty
<b>Supplementary power fuse links - rejection - Class CC.</b>					
<b>KTK-R (A)</b>	1/10 to 30	10 X 38mm	600	Fast	10
<b>LP-CC (A)</b>	1/4 to 30			T/Delay	
<b>FNQ-R (A)</b>	1/4 to 30				



KTK-R

Item no.	Amp	Volts	Poles	Box qty
<b>Fuseholders to suit supplementary power fuse links - Class CC.</b>				
<b>BC6031SQ</b>	30	600	1	1
<b>BC6033SQ</b>			3	



SC

Item no.	Amp rating	Size	Volts	Type	Box qty
<b>Supplementary power fuse links - Class G.</b>					
<b>SC</b>	1/2 to 20	10 X 33	480	T/Delay	
	25, 30	10 X 42			
	35 to 60	10 X 57			