

Specifications



Eaton BR1224L200R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 200 A, B2R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 24 Circuits, Twenty-four pole, 12 Spaces, Three-wire, Single-phase, 120/240V, #1 AWG-300 kcmil Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR1224L200R
UPC	786676447355
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.

Product specifications	
SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Main lug
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	12
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	B2R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources	
CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR1224L200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.



Specifications



Eaton BR1224L200R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 200 A, B2R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 24 Circuits, Twenty-four pole, 12 Spaces, Three-wire, Single-phase, 120/240V, #1 AWG-300 kcmil Cu/Al

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BR1224L200R
UPC	786676447355
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.

Product specifications	
SPECIAL FEATURES	No feed-thru lugs, includes BREQS125 hold-down screw
TYPE	Main lug
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	12
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
WIRE SIZE	#1 AWG-300 kcmil Cu/Al
BOX SIZE	B2R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources	
CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR1224L200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

