

# Eaton BR1224L200R

Catalog Number: BR1224L200R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 200 A, B2R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 24 Circuits, Twenty-four pole, 12 Spaces, Three-wire, Single-phase, 120/240V, #1 AWG-300 kcmil Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR1224L200R
<b>UPC</b>	<b>Product Length/Depth</b>
786676447355	5.19 in
<b>Product Height</b>	<b>Product Width</b>
18.75 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.

## Product specifications

### Special features

No feed-thru lugs, includes BREQS125 hold-down screw

### Type

Main lug

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Number of circuits

24

### Number of spaces

12

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#1 AWG-300 kcmil Cu/Al

### Box size

B2R

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BR1224L200R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)