

Eaton BR1224N200R

Catalog Number: BR1224N200R

Eaton BR convertible loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, Convertible main, 200 A, C3r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 24 Circuits, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR1224N200R
UPC	Product Length/Depth
786676448550	5.19 in
Product Height	Product Width
25 in	14.31 in
Product Weight	Warranty
27 lb	10 year
Certifications	Catalog Notes
UL 67 UL 50	The maximum rating of the panel is the main breaker rating when used as service entrance equipment. Has notch for brhdk125 hold-down kit.

Product specifications

Special features

No feed-thru lugs, includes BREQS125 hold-down screw

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

24

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

C3R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Specifications and datasheets

Eaton Specification Sheet - BR1224N200R

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)