



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR1624B125 16/24C 125A 1PH MB Loadcenter

Eaton Corp

Catalog Number	BR1624B125
Manufacturer	Eaton Corp
Description	BR Style Load Center, 16 Spaces, 24 Circuits, 125 A, 120/240 V Ac, #4 to 2/0 Awg Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 21 In Overall Height
Weight per unit	22.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

### Features

amperage rating	125 VAC
Box Size	08447
cover	Cover included
Cover Type	Cover included
dimensions	5.1900 IN X 14.3100 IN X 18.7500 IN
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

### Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

### Dimensions and Weight

Size	08447
------	-------

### Descriptions

Description	16/24C 125A 1PH MB LOADCENTER
extra long description	ETN BR1624B125 BR style 1-inch load

### Manufacturer Information

GTIN	00786676444408
UPC	786676444408

### Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMESELECT[T] BRAND
Type	Main circuit breaker
unspsc code	39121101



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	22

## Uses, Certifications, and Standards

Enclosure	NEMA 1
Mounting standard	Combination UL 67; UL 50