

# Eaton BR2024B125

Catalog Number: BR2024B125

BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 125A, single-phase, 24-pole, 24 circuits, 20 spaces, 120/240V, #4-2/0 AWG Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c1 box size



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BR2024B125
<b>UPC</b>	<b>Product Length/Depth</b>
786676444453	3.88 in
<b>Product Height</b>	<b>Product Width</b>
16.75 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
24 lb	10 year

## Certifications

UL 67  
UL 50

## Product specifications

### Special features

No feed-thru lugs

### Type

Main circuit breaker

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

24

### Number of spaces

20

### Phase

Single-phase

### Wire size

#4-2/0 AWG Cu/Al

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

C1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

### Specifications and datasheets

Eaton Specification Sheet - BR2024B125

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)