

# Specifications



## Eaton BR2024L125R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 125 A, C1R, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 24 Circuits, Twenty-four pole, 20 Spaces, Three-wire, Single-phase, 120/240V, #6-2/0 AWG Cu/Al

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BR2024L125R
<b>UPC</b>	786676447058
<b>PRODUCT LENGTH/DEPTH</b>	5.19 in
<b>PRODUCT HEIGHT</b>	21 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15.8 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 67 UL 50
<b>CATALOG NOTES</b>	Has notch for brhdk125 hold-down kit.

## Product specifications

<b>SPECIAL FEATURES</b>	No feed-thru lugs, includes BREQS125 hold-down screw
<b>TYPE</b>	Main lug
<b>AMPERAGE RATING</b>	125 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	BR
<b>NUMBER OF CIRCUITS</b>	24
<b>NUMBER OF SPACES</b>	20
<b>PHASE</b>	Single-phase
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240V
<b>WIRE SIZE</b>	#6-2/0 AWG Cu/Al
<b>BOX SIZE</b>	C1R
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	10 kAIC
<b>NUMBER OF WIRES</b>	3

## Resources

### CATALOGS

[Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BR2024L125R](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton BR2024L125R

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, 125 A, C1R, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 24 Circuits, Twenty-four pole, 20 Spaces, Three-wire, Single-phase, 120/240V, #6-2/0 AWG Cu/Al

### General specifications

<b>PRODUCT NAME</b>	Eaton BR main lug loadcenter
<b>CATALOG NUMBER</b>	BR2024L125R
<b>UPC</b>	786676447058
<b>PRODUCT LENGTH/DEPTH</b>	5.19 in
<b>PRODUCT HEIGHT</b>	21 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15.8 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 67 UL 50
<b>CATALOG NOTES</b>	Has notch for brhdk125 hold-down kit.

## Product specifications

<b>SPECIAL FEATURES</b>	No feed-thru lugs, includes BREQS125 hold-down screw
<b>TYPE</b>	Main lug
<b>AMPERAGE RATING</b>	125 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	BR
<b>NUMBER OF CIRCUITS</b>	24
<b>NUMBER OF SPACES</b>	20
<b>PHASE</b>	Single-phase
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240V
<b>WIRE SIZE</b>	#6-2/0 AWG Cu/Al
<b>BOX SIZE</b>	C1R
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	10 kAIC
<b>NUMBER OF WIRES</b>	3

## Resources

### CATALOGS

[Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BR2024L125R](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
[Eaton.com](http://Eaton.com)

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

