



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BR20I BR20I Iv DPLX 5-20R** *Leviton Manufacturing*

Catalog Number	BR20I
Manufacturer	Leviton Manufacturing
Description	20 Amp, 125 Volt, Nema 5-20R, 2P, 3W, Narrow Body Duplex Receptacle, Straight Blade, Commercial Grade, Self Grounding, Back & Side Wired, Steel Strap - Ivory
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

amperage rating	20
connection	Back and Side Wired
Dielectric Strength	2000 (Min.)
Material	Nylon
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wire Size	14-10

### **Material, Color, and Finish**

Color	Ivory
-------	-------

### **Dimensions and Weight**

Depth	19
-------	----

### **Descriptions**

Description	BR20I IV DPLX 5-20R
extra long description	LEV BR20-I SELF GRND DUPL RECEP
Long Description	20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Narrow Body Duplex Receptacle, Straight Blade, Commercial Grade, Self Grounding, Back & Side Wired, Steel Strap - IVORY
Product Type	Self GRND Dupl Recept

### **Manufacturer Information**

Brand	Leviton Manufacturing Company
GTIN	00078477819807
Manufacturers Part Number	BR20-I
UPC	078477819807

### **Taxonomies, Classifications, and Categories**

Category Description	Residential Switches
Type	Duplex Outlet;Straight Blade



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Package	100
Weight Per each	0.2

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability (Rated V-2 per UL94)
Mounting	WALLBOX
nema rating	5-20R
standard	ANSI (C-73);CSA C22.2 No. 42 (File 152105);NEMA (WD-2, WD-1, WD-6);NOM Certified (057);UL Listed 498 (File E13399)
Temperature Rating	-40 to +60