

Eaton BR220B

Catalog Number: BR220B

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, Tapped molded opening, special application, 20 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters

General specifications



Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BR220B

UPC

786676008846

Product Length/Depth

3 in

Product Height

3 in

Product Width

2 in

Product Weight

0.5 lb

Warranty

Limited lifetime residential, 1 year commercial

Compliances

Federal Specifications Classification W-C375

Certifications

UL 489

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Special features

Tapped molded opening, special application

Amperage Rating

20 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR220B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)