

Eaton BR24L125SP

Catalog Number: BR24L125SP

Eaton BR main lug loadcenter, Current design, Main lug, 125 A, 6, Aluminum, Cover not included, NEMA 1, Metallic, 10 kAIC, Surface, 4 Circuits, 2 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V, #14-1/0 AWG Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR24L125SP
UPC	Product Length/Depth
786676002271	3.88 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
5.4 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Ground bar kits priced separately. Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

defaultTaxonomyAttributeLabel

Special features

Current design

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover not included

Mounting

Surface

Number of circuits

4

Number Of Poles

Four-pole

Number of spaces

2

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

#14-1/0 AWG Cu/Al

Box size

6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR24L125SP

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)