

# Eaton BR24L70SP

Catalog Number: BR24L70SP

Eaton BR main lug loadcenter,Current design,Main lug,70 A,5,Aluminum,Cover not included,NEMA 1,Metallic,10 kAIC,BR,Surface,4 Circuits,2 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240 V,#8-2 AWG Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BR24L70SP
<b>UPC</b>	<b>Product Length/Depth</b>
786676001670	3.88 in
<b>Product Height</b>	<b>Product Width</b>
23 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
3.3 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Ground bar kit priced separately. Suitable for use as service equipment when no more than 2 service disconnecting mains are provided or when not used as lighting & appliance panelboard

## defaultTaxonomyAttributeLabel

### Special features

Current design

### Type

Main lug

### Amperage Rating

70 A

### Bus material

Aluminum

### Cover

Cover not included

### Main circuit breaker

BR

### Mounting

Surface

### Number of circuits

4

### Number Of Poles

Four-pole

### Number of spaces

2

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

#8-2 AWG Cu/Al

### Box size

5

### Enclosure

NEMA 1

### Enclosure material

Metallic

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR24L70SP

Interrupt rating

10 kAIC

Number of wires

3



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)