

Eaton BR3040L200R

Catalog Number: BR3040L200R

Eaton BR main lug loadcenter, No feed-thru lugs, 200 A, D1R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 40 Circuits, Twenty-four pole, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1 AWG-300 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR3040L200R
UPC	Product Length/Depth
786676447706	5.19 in
Product Height	Product Width
29.13 in	14.31 in
Product Weight	Warranty
43 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Has notch for brhdk125 hold-down kit.

Product specifications

Special features

No feed-thru lugs

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

D1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Specifications and datasheets

Eaton Specification Sheet - BR3040L200R

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)