



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR3040N200

UPC:786676448857

Dimensions:

- **Height:** 29.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:34 LB

Notes:The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

Warranties:

- 10 year

Specifications:

- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Mounting:** Combination
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** BR2040b199
- **Voltage Rating:** 120/240V
- **Wire Size:** Depends upon main breaker kit or main lug kit chosen.

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters -](#)



Instructions

- Eatons Volume 1-Residential and Light Commercial
- Type BR Arc Fault Circuit Breakers and Loadcenters
- Eaton Specification Sheet - BR3040N200
- Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE

Certifications:

- UL 50
- UL 67

Product compliance: No Data