

Specifications



Photo is representative

Eaton BR3040N200R

Eaton BR convertible loadcenter, Value pack, Convertible main, 200 A, D1r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 40 Circuits, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V, Determined by circuit breaker installed

General specifications

PRODUCT NAME	Eaton BR convertible loadcenter
CATALOG NUMBER	BR3040N200R
UPC	786676448901
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	34 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	40 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.



Product specifications

SPECIAL FEATURES

Value pack

Resources

TYPE	Convertible main
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	30
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
WIRE SIZE	Determined by circuit breaker installed
BOX SIZE	D1R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR3040N200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

