

Specifications

Eaton BR3060BQN200R

Quick connect neutrals, Main circuit breaker loadcenter, 200A, G1R, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 60 circuits, 30 spaces, Three-wire, Single-phase, #2 AWG-300 kcmil, Combination, Type BR 1-inch breakers, 120/240V



General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR3060BQN200R
UPC	786676026253
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	34.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	39 lb
WARRANTY	10 year
CERTIFICATIONS	UL Listed file E52977



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Quick connect neutrals
TYPE	Main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
WIRE SIZE	#2 AWG-300 kcmil
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	G1R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR3060BQN200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton BR3060BQN200R

Quick connect neutrals, Main circuit breaker loadcenter, 200A, G1R, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 60 circuits, 30 spaces, Three-wire, Single-phase, #2 AWG-300 kcmil, Combination, Type BR 1-inch breakers, 120/240V



General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR3060BQN200R
UPC	786676026253
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	34.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	39 lb
WARRANTY	10 year
CERTIFICATIONS	UL Listed file E52977



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Quick connect neutrals
TYPE	Main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	60
NUMBER OF SPACES	30
PHASE	Single-phase
WIRE SIZE	#2 AWG-300 kcmil
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	G1R
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR3060BQN200R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

