



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR3060LQN125G

UPC:786676026338

Dimensions:

- **Height:** 29.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:29 LB

Notes:GBK21 installed

Warranties:

- 10 year

Specifications:

- **Type:** Main lug
- **Amperage Rating:** 125A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Mounting:** Combination
- **Number Of Circuits:** 60
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #6-2/0 AWG Cu/Al at 60°C or 75°C

Supporting documents:

- [Eaton Specification Sheet - BR3060LQN125G](#)

Certifications: No Data

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR3060LQN125G

UPC:786676026338

Dimensions:

- **Height:** 29.13 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:29 LB

Notes:GBK21 installed

Warranties:

- 10 year

Specifications:

- **Type:** Main lug
- **Amperage Rating:** 125A
- **Box Size:** D1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Mounting:** Combination
- **Number Of Circuits:** 60
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #6-2/0 AWG Cu/Al at 60°C or 75°C

Supporting documents:

- [Eaton Specification Sheet - BR3060LQN125G](#)

Certifications: No Data

Product compliance: No Data



