

Eaton BR3060LQN200RG

Catalog Number: BR3060LQN200RG

Eaton BR main lug loadcenter, 200 A,D1R,Aluminum, NEMA 1,Metallic,10 kAIC,Combination,NEMA 1,60 Circuits,Twenty-four pole,30 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#1 AWG-300 kcmil Cu/Al

General specifications



Product Name	Catalog Number
Eaton BR main lug loadcenter	BR3060LQN200RG
UPC	Product Length/Depth
786676026321	5.19 in
Product Height	Product Width
29.13 in	14.31 in
Product Weight	Warranty
35 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	GBK2120 installed

Product specifications

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Mounting

Combination

Number of circuits

60

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

D1R

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Specifications and datasheets

Eaton Specification Sheet - BR3060LQN200RG

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)