

Eaton BR360

Catalog Number: BR360

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 60 A, 10 kAIC, Three-pole, 240V, BR, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR360
	UPC
	786676367950
Product Length/Depth	Product Height
3 in	2.75 in
Product Width	Product Weight
3 in	0.94 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

60 A

Voltage rating

240 V - 240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#4-1/0 AWG Cu/Al

Number of poles

Three-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR360](#)