

# Eaton BR4040N200RG

Catalog Number: BR4040N200RG

Eaton BR convertible loadcenter,Ground bar, includes BREQS125 hold-down screw,Convertible main,200 A,C4,Aluminum,Cover included,NEMA 3R,Metallic,25 kAIC,BWH,Combination,40 Circuits,40 Spaces,Three-wire,Single-phase,120/240 V

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR4040N200RG
UPC	Product Length/Depth
782116893959	3.88 in
Product Height	Product Width
27 in	14.31 in
Product Weight	Warranty
34 lb	10 year

## Certifications

UL 50  
UL 67

## Product specifications

### Special features

Ground bar, includes BREQS125 hold-down screw

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Mounting

Combination

### Number of circuits

40

### Number of spaces

40

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

Determined by circuit breaker installed

### Box size

C4

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BR4040N200RG](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)