



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

BR4242B225

UPC:786676446402

### Dimensions:

- **Height:** 9.44 IN
- **Length:** 3 IN
- **Width:** 4.5 IN

**Weight:**42 LB

### Warranties:

- 10 year

### Specifications:

- **Special Features:** Current design
- **Type:** Main circuit breaker
- **Amperage Rating:** 225A
- **Box Size:** 5
- **Bus Material:** Aluminum
- **Cover:** Cover not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #1 AWG-250 kcmil Cu/Al
- **Mounting:** Flush
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Dimensional Drawing - BR 1 LOADCENTER, CSR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)



- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR4242B225](#)

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.