

Eaton BR48L125FP

Catalog Number: BR48L125FP

Eaton Eaton BR main lug loadcenter ,No feed-thru lugs,Convertible main,200 A,L1,Aluminum,Cover included,NEMA 1,Metallic,25 kAIC,BWH,Combination,NEMA 1,42 Circuits,30 Spaces,Four-wire,Three-phase,Type BR 1-inch breakers

General specifications



Product Name	Eaton BR main lug loadcenter	Catalog Number	BR48L125FP
UPC	786676001717	Product Length/Depth	3.56 in
Product Height	13 in	Product Width	11 in
Product Weight	9.1 lb	Warranty	10 year
Certifications	UL 67 UL 50		

defaultTaxonomyAttributeLabel

Special features

Current design

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover not included

Main circuit breaker

BR

Mounting

Flush

Number of circuits

8

Number Of Poles

Eight-pole

Number of spaces

4

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#14-1/0 AWG Cu/Al

Box size

7

Enclosure

NEMA 1

Enclosure material

Metallic

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR48L125FP

Interrupt rating

10 kAIC

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia