



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR48L125SP 1PH 125A Mlo 4/8 Cir Al Bus Surface Cover

Eaton Corp

|                  |  |
|------------------|--|
| Catalog Number   | BR48L125SP   |
| Manufacturer     | Eaton Corp   |
| Description      | Main Lug Load Center, 4 Spaces, 8 Circuits, 125 A, 120/240 V Ac, #14 to 1/0 Awg Wire Size, Metallic Material, Aluminum Bus Material, 11 In Overall Length, 3.56 In Overall Width, 13 In Overall Height, Surface Mount (Trim) |
| Weight per unit  | 9.1 (lbs/each)   |
| Product Category | Single Phase Main Lug Load Cen   |

### Features

|                 |                    |
|-----------------|--------------------|
| amperage rating | 125                |
| Cover Type      | Cover not included |
| Phase           | 1                  |
| Wattage         | Eight-pole         |

### Dimensions and Weight

|        |      |
|--------|------|
| Depth  | 3.56 |
| Height | 13   |
| Size   | 7    |
| Width  | 11   |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1PH 125A MLO 4/8 CIR AL BUS SURFACE COVER |
| extra long description | ETN BR48L125SP 1 Ph/BR LC 125A MLO        |
| Special Features       | Current design                            |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00786676001236 |
| UPC  | 786676001236   |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | LOADCENTERS & COVERS |
| Type                 | Main lug loadcenter  |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 9.05 |

### Uses, Certifications, and Standards

|          |               |
|----------|---------------|
| Mounting | Surface Mount |
| standard | UL 67,UL 50   |