

# Eaton BRC48L125RP

Catalog Number: BRC48L125RP

Eaton Eaton BR main lug loadcenter, 125 A,6R,Aluminum, NEMA 3R,Metallic,10 kAIC,BR,NEMA 3R,8 Circuits,Eight-pole,4 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#14-1/0 AWG Cu/Al



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRC48L125RP
UPC	Product Length/Depth
786689212575	4.5 in
Product Height	Product Width
11.75 in	6.5 in
Product Weight	Certifications
6.35 lb	UL 50
	UL 67

## defaultTaxonomyAttributeLabel

### Type

Main lug

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

8

### Number Of Poles

Eight-pole

### Number of spaces

4

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#14-1/0 AWG Cu/Al

### Box size

6R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRC48L125RP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)