

# Eaton BRCAF115CS

Catalog Number: BRCAF115CS

Eaton BR AFCI circuit breaker, AFCI Circuit breaker, Clamshell pack, 15 A, 10 kAIC, Single-pole, 120 V, BRC, Pigtail, #14-4 AWG Cu/Al, Q30, Type BR Loadcenters

## General specifications



### Product Name

Eaton BR AFCI circuit breaker

### Catalog Number

BRCAF115CS

### UPC

786685514369

### Product Length/Depth

6 in

### Product Height

1.25 in

### Product Width

3.5 in

### Product Weight

0.45 lb

### Warranty

Limited lifetime residential, 1 year commercial

### Compliances

Federal Specifications Classification W-C375

### Certifications

UL 1699



Powering Business Worldwide

## Type

AFCI Circuit breaker

## Special features

Clamshell pack

## Amperage Rating

15 A

## Voltage rating

120 V

## Used with

Type BR Loadcenters

## Interrupt rating

10 kAIC

## Main circuit breaker

BR

## Connection

Pigtail

## Wire size

#14-4 AWG Cu/Al

## Number of poles

Single-pole

## Quantity

30

## Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

## Catalogs

Eaton's Volume 1—Residential and Light Commercial

## Specifications and datasheets

Type BR (1") Combination Arc Fault Circuit Interrupter

Eaton Specification Sheet - BRCAF115CS