

Eaton BRH2110

Catalog Number: BRH2110

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 110 A, 22 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BRH, Type BR Loadcenters

General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BRH2110
	UPC
	786676374248
Product Length/Depth	Product Height
2.5 in	3 in
Product Width	Product Weight
2 in	0.6 lb
Compliances	Certifications
Federal Specifications Classification W-C376	UL 490
	Catalog Notes
	10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting



defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

110 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

22 kAIC

Main circuit breaker

BRH

Wire size

#4-1/0 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BRH2110](#)