

Specifications



Photo is representative



Eaton BRHX2110

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRHX circuit breaker, 110 A, 22kAIC, Two-pole, 120/240V, BRHX, Non-interchangeable, 110, Plug-on, BRHX

General specifications

PRODUCT NAME	Eaton BR thermal magnetic circuit breaker
CATALOG NUMBER	BRHX2110
UPC	786689041663
PRODUCT LENGTH/DEPTH	2.6 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	1.9 in
PRODUCT WEIGHT	0.75 lb
WARRANTY	1 year
CERTIFICATIONS	Contact Manufacturer
PRODUCT TYPE	Thermal magnetic circuit breakers

EATON

Powering Business Worldwide

Product specifications

AMPERAGE RATING	110
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-interchangeable
CIRCUIT BREAKER TYPE	BR
MOUNTING METHOD	Plug-on
INTERRUPT RATING	22 kAIC
MAIN CIRCUIT BREAKER	BR
CONNECTION	Plug-on
NUMBER OF POLES	Two-pole
TRIP RATING	110 A
TYPE	Quicklag Type BRHX circuit breaker

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRHX2110
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

