

# Eaton BRHX2125

Catalog Number: BRHX2125

Eaton BR thermal magnetic circuit breaker,Quicklag Type BRHX circuit breaker,125 A,22kAIC,Two-pole,120/240V,BRHX,Non-interchangeable,125,Plug-on,BRHX



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BRHX2125
	UPC
	786689041670
<b>Product Length/Depth</b>	<b>Product Height</b>
3.1 in	3 in
<b>Product Width</b>	<b>Product Weight</b>
2.2 in	0.9 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	Contact Manufacturer

## Product specifications

### Type

Quicklag Type BRHX circuit breaker

### Amperage Rating

125

### Voltage rating

120/240 V

### Trip Type

Non-interchangeable

### Circuit breaker type

BR

### Mounting Method

Plug-on

### Interrupt rating

22 kAIC

### Main circuit breaker

BR

### Connection

Plug-on

### Number of poles

Two-pole

### Trip rating

125

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRHX2125](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)