

Specifications

Photo is representative

Eaton BRHX2125

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRHX circuit breaker, 125 A, 22kAIC, Two-pole, 120/240V, BRHX, Non-interchangeable, 125, Plug-on, BRHX

General specifications

PRODUCT NAME	Eaton BR thermal magnetic circuit breaker
CATALOG NUMBER	BRHX2125
UPC	786689041670
PRODUCT LENGTH/DEPTH	3.1 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	Contact Manufacturer

Product specifications

AMPERAGE RATING	125
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-interchangeable
CIRCUIT BREAKER TYPE	BR
MOUNTING METHOD	Plug-on
INTERRUPT RATING	22 kAIC
MAIN CIRCUIT BREAKER	BR
CONNECTION	Plug-on
NUMBER OF POLES	Two-pole
TRIP RATING	125
TYPE	Quicklag Type BRHX circuit breaker

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRHX2125
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

