

# Specifications



Photo is representative



## Eaton BRH2125

Eaton BR thermal magnetic circuit breaker, Quicklag Type BRH circuit breaker, 125 A, 22kAIC, Two-pole, 120/240V, BRH, Non-interchangeable, 125, Plug-on, BRH

### General specifications

<b>PRODUCT NAME</b>	Eaton BR thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	BRH2125
<b>UPC</b>	786689041670
<b>PRODUCT LENGTH/DEPTH</b>	3.1 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	2.2 in
<b>PRODUCT WEIGHT</b>	0.9 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	Contact Manufacturer
<b>PRODUCT TYPE</b>	Thermal magnetic circuit breakers

## Product specifications

<b>AMPERAGE RATING</b>	125
<b>VOLTAGE RATING</b>	120/240 V
<b>TRIP TYPE</b>	Non-interchangeable
<b>CIRCUIT BREAKER TYPE</b>	BR
<b>MOUNTING METHOD</b>	Plug-on
<b>INTERRUPT RATING</b>	22 kAIC
<b>MAIN CIRCUIT BREAKER</b>	BR
<b>CONNECTION</b>	Plug-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TRIP RATING</b>	125
<b>TYPE</b>	Quicklag Type BRHX circuit breaker

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRHX2125](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
[Eaton.com](#)

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

