

Eaton BRP08B200RF

Catalog Number: BRP08B200RF

Feed through lugs, Plug-on neutral main circuit breaker loadcenter, 200A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BR, 16 circuits, Single pole, 8 spaces, Three-wire, Single-phase, Feed-through lugs, Combination, NEMA 3R, Type BR 1-inch brea

General specifications



Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP08B200RF
UPC	Product Length/Depth
786689059101	25 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
18 lb	10 year
Certifications	
UL 50	
UL 67	



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Feed through lugs

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

16

Number Of Poles

Single-pole

Number of spaces

8

Phase

Single-phase

Accessories

Feed-through lugs

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 3R

Enclosure material

Metallic

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP08B200RF

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Interrupt rating

25 kAIC

Number of wires

3

NEMA rating

NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP08B200RF

Catalog Number: BRP08B200RF

Feed through lugs, Plug-on neutral main circuit breaker loadcenter, 200A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BR, 16 circuits, Single pole, 8 spaces, Three-wire, Single-phase, Feed-through lugs, Combination, NEMA 3R, Type BR 1-inch brea

General specifications



Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP08B200RF
UPC	Product Length/Depth
786689059101	25 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
18 lb	10 year
Certifications	
UL 50	
UL 67	



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Feed through lugs

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

16

Number Of Poles

Single-pole

Number of spaces

8

Phase

Single-phase

Accessories

Feed-through lugs

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 3R

Enclosure material

Metallic

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP08B200RF

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Interrupt rating

25 kAIC

Number of wires

3

NEMA rating

NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia