

Eaton BRP10B100

Catalog Number: BRP10B100

Plug-on neutral main circuit breaker loadcenter, 100A, X0, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR, 20 circuits, Single pole, 10 spaces, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG Cu/Al, 25, Kilo Ampere, 10 kAIC, Gray, Combinati



General specifications

| | |
|----------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR main breaker loadcenter | BRP10B100 |
| UPC | Product Length/Depth |
| 786689054939 | 16.75 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 16.5 lb | 10 year |

Certifications

UL 67
UL 50

defaultTaxonomyAttributeLabel

Special features

Main circuit breaker

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

20

Number Of Poles

Single-pole

Number of spaces

10

Phase

Single-phase

Wire size

#6-1/0 AWG Cu/Al

Bus Rating

25 kA

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X0

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP10B100

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Circuit breaker rating

10 kAIC

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP10B100

Catalog Number: BRP10B100

Plug-on neutral main circuit breaker loadcenter, 100A, X0, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR, 20 circuits, Single pole, 10 spaces, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG Cu/Al, 25, Kilo Ampere, 10 kAIC, Gray, Combinati



General specifications

| | |
|----------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR main breaker loadcenter | BRP10B100 |
| UPC | Product Length/Depth |
| 786689054939 | 16.75 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 16.5 lb | 10 year |

Certifications

UL 67
UL 50

defaultTaxonomyAttributeLabel

Special features

Main circuit breaker

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

20

Number Of Poles

Single-pole

Number of spaces

10

Phase

Single-phase

Wire size

#6-1/0 AWG Cu/Al

Bus Rating

25 kA

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X0

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP10B100

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Circuit breaker rating

10 kAIC

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)