

# Eaton BRP12L125G

Catalog Number: BRP12L125G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 125 A, X0, Aluminum, NEMA 1, Metallic, 10kAIC, BR2125, Surface, flush, 24 Circuits, Twenty-four pole, 12 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V



## General specifications

|                              |                      |
|------------------------------|----------------------|
| Product Name                 | Catalog Number       |
| Eaton BR main lug loadcenter | BRP12L125G           |
| UPC                          | Product Length/Depth |
| 786689053000                 | 16.75 in             |
| Product Height               | Product Width        |
| 3.88 in                      | 14.31 in             |
| Product Weight               | Warranty             |
| 16.1 lb                      | 10 year              |

## Certifications

UL 67  
UL 50

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR2125

### Mounting

Surface, flush

### Number of circuits

24

### Number Of Poles

Single-pole

### Number of spaces

12

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#6-2/0 AWG Cu/Al

### Box size

X0

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP12L125G](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)