

# Eaton BRP12N125G

Catalog Number: BRP12N125G

Eaton BR convertible loadcenter, Ground bar, Plug-on neutral main circuit breaker loadcenter, 125A, X1, Aluminum, Cover included, NEMA 1, Metallic, 25kAIC, BR, 24 circuits, 1P, 12 spaces, 2 hots, neutral and ground, Single-phase, #6-1/0AWG Cu/Al, 25, KA



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR convertible loadcenter	BRP12N125G
<b>UPC</b>	<b>Product Length/Depth</b>
786689054953	18.75 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
17 lb	10 year
<b>Certifications</b>	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Special features

Ground bar

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

24

### Number Of Poles

Single-pole

### Number of spaces

12

### Phase

Single-phase

### Wire size

#6-1/0 AWG Cu/Al

### Accessories

ground bar

### Bus Rating

25 kA

### Enclosure color

Gray

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP12N125G](#)

Box size

X1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)