

Eaton BRP12N125R

Catalog Number: BRP12N125R

Eaton BR convertible loadcenter, Convertible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 24 Circuits, Single-pole, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP12N125R
UPC	Product Length/Depth
786689059170	3.88 in
Product Height	Product Width
25 in	14.31 in
Product Weight	Warranty
18 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Type

Convertible

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

24

Number Of Poles

Single-pole

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP12N125R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP12N125R

Catalog Number: BRP12N125R

Eaton BR convertible loadcenter, Convertible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 24 Circuits, Single-pole, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP12N125R
UPC	Product Length/Depth
786689059170	3.88 in
Product Height	Product Width
25 in	14.31 in
Product Weight	Warranty
18 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Type

Convertible

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

24

Number Of Poles

Single-pole

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP12N125R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)