

Eaton BRP16B200

Catalog Number: BRP16B200

Plug-on neutral main circuit breaker loadcenter,200A,X4,Aluminum,Cover included,NEMA 1,Metallic,25kAIC,CSR2200,32 circuits,Single pole,16 spaces,Two hots, a neutral, and a ground,Single-phase,Gray,Combination,NEMA 1,Type BR 1-inch breakers,



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP16B200
UPC	Product Length/Depth
786689053109	27 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
25.85 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP16B200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP16B200

Catalog Number: BRP16B200

Plug-on neutral main circuit breaker loadcenter,200A,X4,Aluminum,Cover included,NEMA 1,Metallic,25kAIC,CSR2200,32 circuits,Single pole,16 spaces,Two hots, a neutral, and a ground,Single-phase,Gray,Combination,NEMA 1,Type BR 1-inch breakers,



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP16B200
UPC	Product Length/Depth
786689053109	27 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
25.85 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X4

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP16B200

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)