

Specifications



Photo is representative



Eaton BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0

General specifications

| | |
|-----------------------------|------------------------------|
| PRODUCT NAME | Eaton BR main lug loadcenter |
| CATALOG NUMBER | BRP16L125R |
| UPC | 786689059200 |
| PRODUCT LENGTH/DEPTH | 3.88 in |
| PRODUCT HEIGHT | 18.75 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 15 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 67 UL 50 |
| PRODUCT TYPE | Main lug loadcenter |



Powering Business Worldwide

Product specifications

| | |
|-----------------------------|-------------------------|
| TYPE | MLO |
| AMPERAGE RATING | 125 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BR |
| NUMBER OF CIRCUITS | 32 |
| NUMBER OF POLES | Single-pole |
| NUMBER OF SPACES | 16 |
| PHASE | Single-phase |
| USED WITH | Type BR 1-inch breakers |
| VOLTAGE RATING | 120/240V |
| BOX SIZE | X1 |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 10 kAIC |
| NEMA RATING | NEMA 3R |
| NUMBER OF WIRES | 3 |

Resources

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - BRP16L125R |
| WARRANTY GUIDES | Eaton type BR circuit breaker limited warranty June 2024 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

