

# Eaton BRP20B125R

Catalog Number: BRP20B125R

Plug-on neutral main circuit breaker loadcenter, 125A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Single pole, 20 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V



## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP20B125R
UPC	Product Length/Depth
786689059262	23 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
18 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X4

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP20B125R](#)

NEMA rating

NEMA 3R

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)