

# Eaton BRP20B150

Catalog Number: BRP20B150

Plug-on neutral main circuit breaker loadcenter, 150A, X4, Aluminum, Cover included, NEMA 1, Metallic, 25kAIC, CSR2150, 40 circuits, Single pole, 20 spaces, Two hots, a neutral, and a ground, Single-phase, Gray, Combination, NEMA 1, Type BR 1-inch breakers,



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP20B150
<b>UPC</b>	<b>Product Length/Depth</b>
786689053178	27 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
26.2 lb	10 year
<b>Certifications</b>	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

150 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR2150

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Enclosure color

Gray

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X4

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BRP20B150

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)