

# Eaton BRP20L150

Catalog Number: BRP20L150

Eaton Eaton BR main lug loadcenter, Main lug only, 150 A, X3, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2125, NEMA1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BRP20L150
<b>UPC</b>	<b>Product Length/Depth</b>
786689053246	23 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
21 lb	10 year
<b>Certifications</b>	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

150 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR2125

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Box size

X3

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### NEMA rating

NEMA 1

### Number of wires

Two hots, neutral and ground

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BRP20L150



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)