

Eaton BRP20L200R

Catalog Number: BRP20L200R

Eaton Eaton BR main lug loadcenter, Main lug only, 200 A, X4, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil

General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP20L200R
UPC	Product Length/Depth
786689059286	3.88 in
Product Height	Product Width
5.7 in	14.31 in
Product Weight	Warranty
18 lb	10 year
Certifications	
UL 50 UL 67	

Product specifications

Number of spaces

20

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Main circuit breaker

BR

Enclosure

NEMA 3R

Amperage Rating

200 A

Number Of Poles

Single-pole

Enclosure material

Metallic

Type

MLO

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 3R

Number of wires

3

Number of circuits

40

Voltage rating

120/240V

Box size

X4

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP20L200R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)