

Eaton BRP20N125

Catalog Number: BRP20N125

Eaton BR convertible loadcenter, Convertible, 125 A, X2, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP20N125
UPC	Product Length/Depth
786689053284	23 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
20.5 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20N125

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP20N125

Catalog Number: BRP20N125

Eaton BR convertible loadcenter, Convertible, 125 A, X2, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP20N125
UPC	Product Length/Depth
786689053284	23 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
20.5 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20N125

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia