

# Eaton BRP20N125R

Catalog Number: BRP20N125R

Eaton BR convertible loadcenter, Convertible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



Photo is representative

## General specifications

|                                 |                             |
|---------------------------------|-----------------------------|
| <b>Product Name</b>             | <b>Catalog Number</b>       |
| Eaton BR convertible loadcenter | BRP20N125R                  |
| <b>UPC</b>                      | <b>Product Length/Depth</b> |
| 786689059316                    | 3.88 in                     |
| <b>Product Height</b>           | <b>Product Width</b>        |
| 25 in                           | 14.31 in                    |
| <b>Product Weight</b>           | <b>Warranty</b>             |
| 18 lb                           | 10 year                     |

## Certifications

UL 67  
UL 50

## Product specifications

### Type

Convertible

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X4

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP20N125R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRP20N125R

Catalog Number: BRP20N125R

Eaton BR convertible loadcenter, Convertible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



Photo is representative

## General specifications

|                                 |                             |
|---------------------------------|-----------------------------|
| <b>Product Name</b>             | <b>Catalog Number</b>       |
| Eaton BR convertible loadcenter | BRP20N125R                  |
| <b>UPC</b>                      | <b>Product Length/Depth</b> |
| 786689059316                    | 3.88 in                     |
| <b>Product Height</b>           | <b>Product Width</b>        |
| 25 in                           | 14.31 in                    |
| <b>Product Weight</b>           | <b>Warranty</b>             |
| 18 lb                           | 10 year                     |

## Certifications

UL 67  
UL 50

## Product specifications

### Type

Convertible

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X4

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP20N125R](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)