

# Eaton BRP20N200RG

Catalog Number: BRP20N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR convertible loadcenter	BRP20N200RG
<b>UPC</b>	<b>Product Length/Depth</b>
786689059309	3.88 in
<b>Product Height</b>	<b>Product Width</b>
29.13 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
19 lb	10 year

## Certifications

UL 67

UL 50

## Product specifications

### Special features

Ground bar

### Type

Convertible

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP20N200RG](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

3



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)