

Eaton BRP24L125

Catalog Number: BRP24L125

Eaton Eaton BR main lug loadcenter ,Ground bar,Main lug only,125 A,X0,Aluminum,Cover included,NEMA 1,Metallic,10kAIC,BR2125,Surface, flush,NEMA 1,24 Circuits,Twenty-four pole,12 Spaces,Two hots, a neutral



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP24L125
UPC	Product Length/Depth
786689053352	23 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
20 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

MLO

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR2125

Mounting

Surface, flush

Number of circuits

48

Number Of Poles

Single-pole

Number of spaces

24

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-1/0 AWG Cu/Al

Box size

X3

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP24L125](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)