

# Eaton BRP30B150

Catalog Number: BRP30B150

Eaton Plug-on neutral main circuit breaker loadcenter, 150A, X6, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR2125, 60 circuits, Single pole, 30 spaces, Two hots, a neutral, and a ground, Single-phase, Combination, Type BR 1-inch breakers

## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP30B150
UPC	Product Length/Depth
786689053406	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
31.1 lb	10 year
Certifications	
UL 50 UL 67	



## Product specifications

### Number of spaces

30

### Interrupt rating

25 kAIC

### Phase

Single-phase

### Bus material

Aluminum

### Main circuit breaker

CSR2125

### Enclosure

NEMA 1

### Amperage Rating

150 A

### Number Of Poles

Single-pole

### Mounting

Combination

### Enclosure material

Metallic

### Type

Plug-on neutral main circuit breaker loadcenter

### Cover

Cover included

### Used with

Type BR 1-inch breakers

### Number of wires

Two hots, neutral and ground

### Number of circuits

60

### Voltage rating

120/240 V

### Box size

X6

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP30B150](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)