

Eaton BRP30E200G

Catalog Number: BRP30E200G

Eaton BR convertible loadcenter, Convertible, lugs installed, Ground bar, 200 A, X6, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 60 Circuits, Single-pole, 30 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP30E200G
UPC	Product Length/Depth
786689055004	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
29.2 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Convertible, lugs installed
Ground bar

Type

Convertible, lugs installed

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

#6-1/0 AWG Cu/Al

Box size

X6

Enclosure

NEMA 1

Enclosure material

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30E200G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP30E200G

Catalog Number: BRP30E200G

Eaton BR convertible loadcenter, Convertible, lugs installed, Ground bar, 200 A, X6, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 60 Circuits, Single-pole, 30 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP30E200G
UPC	Product Length/Depth
786689055004	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
29.2 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Convertible, lugs installed
Ground bar

Type

Convertible, lugs installed

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

#6-1/0 AWG Cu/Al

Box size

X6

Enclosure

NEMA 1

Enclosure material

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30E200G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)