

# Eaton BRP30L200GW

Catalog Number: BRP30L200GW

Eaton Eaton BR main lug loadcenter, Indoor, Main lug only, 200 A, X5, Aluminum, NEMA 1, Metallic, 10kAIC, CSR2200, Surface, flush, NEMA 1, 60 Circuits, Twenty-four pole, 30 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V, #1–300 kcmil



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BRP30L200GW
<b>UPC</b>	<b>Product Length/Depth</b>
786689052904	29.12 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
26.3 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## Product specifications

### Type

MLO

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR2200

### Mounting

Surface, flush

### Number of circuits

60

### Number of poles

Single-pole

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### NEMA rating

NEMA 1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP30L200GW](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)