

Specifications



Powering Business Worldwide

Eaton BRP30L200GW

Eaton Eaton BR main lug
loadcenter,Indoor,Main lug only,200
A,X5,Aluminum, NEMA
1,Metallic,10kAIC,CSR2200,Surface,flush,NEMA
1,60 Circuits,Twenty-four pole,30 Spaces,Two
hots,a neutral,and a ground,Single-
phase,120/240V,#1-300 kcmil

General specifications	
PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP30L200GW
UPC	786689052904
PRODUCT LENGTH/DEPTH	29.12 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26.3 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications

TYPE	MLO
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	CSR2200
MOUNTING	Surface, flush
NUMBER OF CIRCUITS	60
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	30
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
BOX SIZE	X5
ENCLOSURE	NEMA 1
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 1
NUMBER OF WIRES	Two hots, neutral and ground

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP30L200GW
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

